

Filter Data Sheet


High Purity - General Grade PES

Hydrophilic Polyethersulfone (PES) Membrane for Liquid Applications

General Grade PES Cartridges are designed for general purpose use wherever a cost-effective membrane filter is required. General Grade PES cartridges are inherently hydrophilic. These cartridges offer excellent flow characteristics, excellent service life and broad chemical compatibility. The Extended Area option (GGPESX) offers up to 40% more surface area. This additional area results in significant increases in flowrate and loading capacity in the same footprint.



Flow Rate vs Pressure Drop



* Data represents GGPES. For GGPESX option, multiply given flowrate by 1.4.

Typical Applications

- · Deionized Water Systems
- General-Use Water Filtration
- Liquid Clarification
- · Recirculating Fluids
- · Chemical Filtration

Construction Materials

Membrane	Polyethersulfone			
Support Media	Polypropylene			
End Caps	Polypropylene			
Center Core	Polypropylene			
Outer Support Cage	Polypropylene			
O-Rings/Gaskets	Buna, EPDM, Silicone,			
Viton®, Teflon® Encapsulated Viton				

Sanitization/Sterilization

Filtered Hot Water	80°C for 30 min.
Steam Sterilization	121°C for 30 min.,
	multiple cycles

Chemicals: Cartridges are chemically compatible with most chemicals and sanitizing agents.

Note: Stainless steel insert option needed for all cartridges being hot water sanitized or steam sterilized.

Dimensions

Length:

10 to 40 inches (25.4 to 101.6 cm) nominal

Outside Diameter:

2.70 inches (7.0 cm) nominal

Maximum Recommended Operating Conditions

Temperature......176°F (80°C)

Maximum Differential Pressures

Forward	. 50 PSI (3.4	bar) at 20°0
Reverse	. 40 PSI (2.7	bar) at 20°C

FDA Listed Materials

Manufactured from materials which are listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations.

Toxicity

All polypropylene components meet the specifications for biological safety per USP Class VI – 121°C for plastics.

Ordering Information

-							
GGPES	Rating (μ)	Α	Length	C	End Cap Style	O-Rings/Gaskets	Adders
GGPESX	0.04		10" (25.4 cm)		2 = DOE Flat Gasket	B = Buna	I = Stainless Steel Insert
	0.1		20" (50.8 cm)		3 = 222 w/ Fin	E = EPDM	CS = 316ss Compression Spring
	0.2		30" (76.2 cm)		4 = 222 w/ Flat Cap	S = Silicone	R = 18 Megohm Rinse
	0.45		40" (101.6 cm)		6 = 226 w/ Flat Cap	V = Viton®	
	0.65				7 = 226 w/ Fin	T = Teflon® Encapsulated Viton®	
	0.8				16 = 213 Internal O-Ring	Z = Teflon® Encapsulated Silicone	

DISCLAIMER: Filtration data presented is representative of performance observed in controlled laboratory testing. It is not given as a warranty, specification or statement of fitness for use. Specific performance can vary widely depending on contaminant type, fluid properties, flow rates and environmental conditions. It is recommended that users conduct thorough qualification testing to assure the product functions as required.